

MKK Film Capacitor

Material Data Sheet

Product Class	Film capacitors B25674xx PhaseCap Energy	
Date	18/11/2019	
IMDS ID if available	NA	
Version	5.02.1a (03/2019)	

Product Part (IMDS: semi component)	Material Class (IMDS: Material)	Material (Classification) VDA 231	Substance	TMPS**) [wt-%]	CAS if applicable	typical mass of material [wt-%]	Traces see 1)
Active Part	Thermoplastic	2A	PP	100	9003-07-0	46	
	Heavy metal	1C	Zn	94	7440-66-6	1.6	
		1B	AL	6	7429-90-5		
	Thermoplastic	2A	Polyamide	100	628-02-4	1.9	
	Heavy metal	1C	Zn	100	7440-66-6	12.4	
Encapsulation	Light metal	1B	Al	97	7429-90-5	3.5	
			Mg	3	7439-95-4		
	Thermoplastic	2A	Polyamide	100	628-02-4	9	
	Organic solid	4B	Adhesive & Sealers	100	7727-37-9	0.2	
	Light metal	1B	Al	100	7429-90-5	13.3	
	Operating supply	6G	N2	100	7727-37-9	0.1	
	Thermoplastic	2A	Polyester	100	25038-59-9	1.2	
	Iron & Steel	1A	Fe	100	7439-89-6	0.2	
Termination	Heavy metal	1C	Sn	99.3	7440-31-5	1.2	
			Cu	0.7	7440-50-8		
	Heavy metal	1C	Cu	99.8	7440-50-8	1.3	
			Sn	0.2	7440-31-5		
	Heavy Metal	1C	Cu	100	7440-50-8	3.5	
	Thermoplastic	2A	PA66	95	628-02-4	2.3	
			Fe	5	7439-86-6		
Mineral material	3B	Ceramic	100	13376-74-4			
Heavy Metals	1C	Brass Alloy	97		2.6		
	1C	Pb	3	7439-92-2			
	Iron & Steel	1A	Fe	100	7439-89-6	0.2	
Mounting Part	Iron & Steel	1A	Fe	98	7439-89-6		
	Heavy metal	1C	Zn	2	7440-66-6	1.5	
Sum in total:						100	

sizes [mm]	weight range [kg]	sizes [mm]	weight range [kg]	sizes [mm]	weight range [kg]	sizes [mm]	weight range [kg]	Part Number
75 x 164	0.7	85 x 200	1.1	100 x 224	1.7	125 x 192	2.3	B25674xx
75 x 185	0.8	85 x 218	1.2	116 x 192	1.9	125 x 207	2.4	
75 x 200	0.8	100 x 192	1.4	116 x 207	2.1	136 x 192	2.7	
75 x 218	0.9	100 x 207	1.6	116 x 224	2.3	136 x 207	2.9	
85 x 185	1.0							

Not part of a Product Class	
Contact	Anant Marathe
Division	CAP FILM, PFC, R&D
Address	TDK India Pvt. Ltd , E22-25, 25-1, MIDC Satpur, Nashik-7, INDIA
	Tel: +91 253 2205117 mailto: anant.marathe@tdk-electronics.tdk.com
*) others: .(not declarable or prohibited substances acc. GADSL)	
**) typical mass percentage of substance	
Important remarks:	
1) The declaration limit is 0.1% as defined by IEC 62474 (IEC PAS 61906). Traces are product parts, substances etc. that are below a percentage of 0.1 % by weight, if not otherwise regulated	
2) This Material Data Sheet contains typical values of the respective products set forth herein. We expressly point out that all values and statements contained herein are based on our best present knowledge and cannot be regarded as binding statements or binding product specifications, unless otherwise explicitly agreed in writing. TDK ELECTRONICS AG AND ITS AFFILIATES HEREBY EXPRESSLY DISCLAIM ANY REPRESENTATION OR WARRANTY, WHETHER EXPRESS, IMPLIED OR STATUTORY, WITH REGARD TO THE STATEMENTS AND VALUES CONTAINED HEREIN, INCLUDING BUT NOT LIMITED TO ANY REPRESENTATION OR WARRANTY OF MERCHANTABILITY OR SUITABILITY FOR ANY PURPOSE.	

The products set forth herein are "RoHS-compatible". RoHS-compatible means that products are compatible with the requirements according to Art. 4 (substance restrictions) of Directive 2011/65/EU of the European Parliament and of the Council of June 8th, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment.

RoHS - Exemptions for the Product Class / Product according to Annex III: (valid not valid)

no exemptions;

Exemption 6 (a): Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0,35 % lead by weight;

Exemption 6 (b): Lead as an alloying element in aluminium containing up to 0,4 % lead by weight;

Exemption 6 (c): Copper alloy containing up to 4 % lead by weight;

Exemption 7 (a): Lead in high melting temperature type solder (i.e. lead-based alloys containing 85 % by weight or more lead);

Exemption 7 (c)-I: Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound;

Exemption 7 (c)-II: Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher;

Exemption 7 (c)-III: Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC;

Exemption 15: Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit Flip Chip packages;

Other Exemption than above